

System 930 Analog Port 1-24 Pin Connection Chart

Pin Number	Wire Color	Description
26	WHT-BLU	T Analog Port 1
1	BLU-WHT	R
27	WHT-ORN	T Analog Port 2
2	ORN-WHT	R
28	WHT-GRN	T Analog Port 3
3	GRN-WHT	R
29	WHT-BRN	T Analog Port 4
4	BRN-WHT	R
30	WHT-SLT	T Analog Port 5
5	SLT-WHT	R
31	RED-BLU	T Analog Port 6
6	BLU-RED	R
32	RED-ORN	T Analog Port 7
7	ORN-RED	R
33	RED-GRN	T Analog Port 8
8	GRN-RED	R
34	RED-BRN	T Analog Port 9
9	BRN-RED	R
35	RED-SLT	T Analog Port 10
10	SLT-RED	R
36	BLK-BLU	T Analog Port 11
11	BLU-BLK	R
37	BLK-ORN	T Analog Port 12
12	ORN-BLK	R
38	BLK-GRN	T Analog Port 13
13	GRN-BLK	R
39	BLK-BRN	T Analog Port 14
14	BRN-BLK	R
40	BLK-SLT	T Analog Port 15
15	SLT-BLK	R
41	YEL-BLU	T Analog Port 16
16	BLU-YEL	R
42	YEL-ORN	T Analog Port 17
17	ORN-YEL	R
43	YEL-GRN	T Analog Port 18
18	GRN-YEL	R
44	YEL-BRN	T Analog Port 19
19	BRN-YEL	R
45	YEL-SLT	T Analog Port 20
20	SLT-YEL	R
46	VIO-BLU	T Analog Port 21
21	BLU-VIO	R
47	VIO-ORN	T Analog Port 22
22	ORN-VIO	R
48	VIO-GRN	T Analog Port 23
23	GRN-VIO	R
49	VIO-BRN	T Analog Port 24
24	BRN-VIO	R
50	VIO-SLT	No Connect
25	SLT-VIO	No Connect

RJ11 Analog Port
 Connections 1-4

938 Analog Card 1
 (Installed in slot 1)

938 Analog Card 2
 (Installed in slot 2)

938 Analog Card 3
 (Installed in slot 3)

System 930 Analog Port 25-32 Pin Connection Chart

Pin Number	Wire Color	Description
26	WHT-BLU	T Analog Port 25
1	BLU-WHT	R
27	WHT-ORN	T Analog Port 26
2	ORN-WHT	R
28	WHT-GRN	T Analog Port 27
3	GRN-WHT	R
29	WHT-BRN	T Analog Port 28
4	BRN-WHT	R
30	WHT-SLT	T Analog Port 29
5	SLT-WHT	R
31	RED-BLU	T Analog Port 30
6	BLU-RED	R
32	RED-ORN	T Analog Port 31
7	ORN-RED	R
33	RED-GRN	T Analog Port 32
8	GRN-RED	R
34	RED-BRN	No Connect
9	BRN-RED	No Connect
35	RED-SLT	No Connect
10	SLT-RED	No Connect
36	BLK-BLU	No Connect
11	BLU-BLK	No Connect
37	BLK-ORN	No Connect
12	ORN-BLK	No Connect
38	BLK-GRN	No Connect
13	GRN-BLK	No Connect
39	BLK-BRN	No Connect
14	BRN-BLK	No Connect
40	BLK-SLT	No Connect
15	SLT-BLK	No Connect
41	YEL-BLU	No Connect
16	BLU-YEL	No Connect
42	YEL-ORN	No Connect
17	ORN-YEL	No Connect
43	YEL-GRN	No Connect
18	GRN-YEL	No Connect
44	YEL-BRN	No Connect
19	BRN-YEL	No Connect
45	YEL-SLT	No Connect
20	SLT-YEL	No Connect
46	VIO-BLU	No Connect
21	BLU-VIO	No Connect
47	VIO-ORN	No Connect
22	ORN-VIO	No Connect
48	VIO-GRN	No Connect
23	GRN-VIO	No Connect
49	VIO-BRN	No Connect
24	BRN-VIO	No Connect
50	VIO-SLT	No Connect
25	SLT-VIO	No Connect

938 Analog Card 4
 (Installed in slot 4)